

1. Product Overview

SprayAway[™] is a heavy-duty, streak-free surface cleaner developed for resin 3D printing environments and general-purpose use. Formulated in-house for cleaning 3D printers and associated equipment, it effectively removes sticky resin residue, grease, and grime while remaining safe for delicate surfaces such as MSLA LCD screens and touch panels.

The non-flammable, low-residue formula leaves surfaces, equipment and tools clean and clear, making SprayAway[™] ideal for resin printing work-spaces as well as a versatile surface cleaner for homes and vehicles.

2. Key Features & Benefits

- ✓ Removes sticky resin residue, grease, and grime
- ✓ Streak-free finish on glass, screens, and smooth surfaces
- ✓ Safe for MSLA LCD screens, touch screens, and printer lids
- ✓ Non-flammable and low odour for safer use
- ✓ Disinfects surfaces and kills 99.8% of bacteria
- ✓ Fresh lemongrass and lime scent
- ✓ Designed and tested for resin 3D printing environments

3. Applications

- ★ Cleaning resin 3D printers including MSLA, DLP, and SLA surfaces
- ★ Cleaning LCD screens, touch screens, and printer enclosures
- ★ Benchtops, MessMatts, tools, and work surfaces
- ★ Ultrasonic cleaner exteriors and surrounding equipment
- ★ Glass, mirrors, windows, and plastic surfaces
- ★ General household and automotive surface cleaning

4. Physical Properties

Property	Value	Test Method
Viscosity	~10 seconds (DIN 4 cup @ 20°C)	Internal QC
Odour	Low	Organoleptic
Shelf Life	36 months	Internal QC

5. Equipment Compatibility

- Compatible with resin 3D printers and post-curing equipment.
- Suitable for use in wash and cure stations, ultrasonic cleaners, and industrial parts washers.
- For cleaning bench tops, glassware, mirrors, household, and automotive surfaces, use SprayAway[™], which is formulated specifically for general surface cleaning and residue-free finishing.

10. Disclaimer

The information provided is based on laboratory testing and practical use. Results may vary depending on printing conditions, equipment, and handling. Users must test compatibility with their equipment and materials prior to regular use. Monocure3D accepts no liability for misuse or application outside recommended guidelines.

6. Directions for Use

1. Spray directly onto the surface to be cleaned, ensuring even coverage.
2. Wipe the surface using a lint-free cloth or paper towel to remove resin, grease, or grime.
3. Repeat if required for heavier buildup or stubborn contamination.
4. Allow the surface to air dry to achieve a streak-free finish.
5. For stubborn resin or grease buildup, use ResinAway® EZY-WIPES[™] if required. Test on an inconspicuous area before use.

7. Health & Safety Information

- **Keep out of reach of children & animals**
- **Use in a well-ventilated area**
- **Avoid eye contact, rinse with water if contact occurs**
- **Refer to SDS (Safety Data Sheet) for complete handling guidelines** www.monocure3d.com.au

8. Storage & Handling

- **Store between 10°C and 40°C** away from direct sunlight
- **Shelf life minimum 36 months** when stored correctly
- **Non-flammable and non-hazardous**
- **Dispose** of according to local waste regulations

9. Ordering Information

- **Product code:** SA-4138TB
- **Sizes:** 750ml Spray Bottle & 2L containers
- **Colour:** Trans Blue
- **Scent(s):** Lemongrass & Lime
- **Where to Buy:** Available through **Monocure3D resellers**
- For technical support or bulk orders, contact:
support@monocure3d.com.au | www.monocure3d.com.au